

Date Project

Notes

STATIC WHITE SERIES 2 RIBBONLYTE 2.2

Our Series 2 Static White RibbonLyte provides a 40% or more increase in lumens per watt, lumens per foot and LEDs per foot. Our Series 2 product line offers a 90+ CRI with tighter LED spacing and shorter cuttable lengths for improved design flexibility.

- 2.2 W/ft (7.2 W/m)
- Create a custom fixture with our channels
- 9 white color temperatures
- 90+ CRI
- 2-Step MacAdam ellipse binning

Applications:

Commercial Entertainment Healthcare Hospitality Museums Public Spaces Residential

Retail





RoHS

IP20

IP65* **IP68**

* 1800K, 2000K, 2200K are not available in IP65 and IP68








ORDERING GUIDE

Category	CRI	Ribbon Type & IP Rating	Wattage & Color	
RB	90			
RB - RIBBONLYTE	90 - 90+ CRI Static White	SWS220 - Static White Series 2 IP20	2.218 - 2.2 W/ft 1800K (IP20 Only)	2.230 - 2.2 W/ft 3000K
		SWS265 - Static White Series 2 IP65	2.220 - 2.2 W/ft 2000K (IP20 Only)	2.235 - 2.2 W/ft 3500K
		(2400K, 2700K, 3000K, 3500K, 4000K, 6000K Only)	2.222 - 2.2 W/ft 2200K (IP20 Only)	2.240 - 2.2 W/ft 4000K
		SWS268 - Static White Series 2 IP68	2.224 - 2.2 W/ft 2400K	2.260 - 2.2 W/ft 6000K
		(2400K, 2700K, 3000K, 3500K, 4000K, 6000K Only)	2.227 - 2.2 W/ft 2700K	

CONNECTION OPTIONS



Standard cable length if not specified:

- ${f 1.}$ 12 in. cable with bare wire (custom length up to 20 feet)
- 2. Standard 12 in. cable with IP67 connectors (custom length up to 10 feet)
- 3. Daisy chain with 3 in. cable between runs (custom length up to 36 in.)
- 4. 3 in. cable between IP67 connector and RibbonLyte (custom length up to 18 in.)
- **5.** Standard 12 in. cable with bare wire (custom length up to 10 feet) Note: IP67 connectors are used for both IP20 and IP65/IP68 RibbonLyte

AVAILABLE COLOR TEMPERATURES





SPECIFICATIONS / DIAGRAM / USAGE GUIDELINES

				STATIC WHITE	SERIES 2 RIBBO	ONLYTE 2.2			
Operating Voltage					24 V				
Power Consumption				2.2	W/ft (7.2 W/m)				
Current (mA) - 24V				92 m	A/ft (302 mA/m	1)			
LED Pitch				49 LEC	s/ft (160 LEDs/	m)			
Protection Rating			IP20, IP65, IP	68 (1800K, 2000	OK, and 2200K a	are only available	e in IP20)		
Dimming/Control	MLV / 0-10 Vol	t / Lutron Hi-lum	ne 1% dimming & H	li-lume Premier (0.1% L3D0 LED (drivers / Lutron '	VIVE code com	pliance available	/ ELV / DALI
Operating Temperature				-40° F to 15	58° F (-40° C to	70° C)			
Colors Temperatures	1800K	2000K	2200K	2400K	2700K	3000K	3500K	4000K	6000K
MacAdam Ellipses (SDCM)				2-	Step Binning				
Lumens	183 lm/ft (599 lm/m)	211 lm/ft (693 lm/m)	233 lm/ft (765 lm/m)	244 lm/ft (801 lm/m)	264 lm/ft (866 lm/m)	268 lm/ft (880 lm/m)	279 lm/ft (916 lm/m)	293 lm/ft (960 lm/m)	281 lm/ft (934 lm/m)
Binning Tolerance					+/- 100K				
LED Beam Angle					120°				
Lamp Life					50,000 Hrs				
Cuttable Length				1.9	96 in (50 mm)				
CRI - All Color Temp.			_		90+ CRI				
Lumens/Watt	83 lm/W	96 lm/W	105 lm/W	111 lm/W	120 lm/W	122 lm/W	127 lm/W	133 lm/W	128 lm/W
Constant Voltage					✓				
Certifications	UL 2108 Issued: 2016/06/17 Ed: 1 Rev: 2021/10/16 Low Voltage Lighting Systems. CSA C22.2 No. 250.0, General Requirements for Luminaires. ROHS compliant UL 2108.								
Warranty				IP20: 6 ye	ears, IP65/68: 3	years			

24V DIMENSIONS	Top View	Side View	Dimensions
IP20	CUTTABLE EVERY: 1.96 in (50 mm)		Width 0.31 in (8 mm) Max Length* 42 ft (12.8 m) Height 0.06 in (1.45 mm)
IP65	CUTTABLE EVERY: 1.96 in (50 mm)	Пэт	Width 0.31 in (8 mm) Max Length* 32.8 ft (10 m) Height 0.1 in (2.5 mm)
1968	CUTTABLE EVERY: 1.96 in (50 mm)	Tr-T-11	Width 0.44 in (11.18 mm) Max Length* 32.8 ft (10 m) Height 0.18 in (4.5 mm)

USAGE GUIDELINES

- IP65 and IP68 RibbonLyte are not field cuttable. All custom cuts and connections for these models must be performed at the factory to ensure waterproofing standards are met. Any modification of this on the field or by end user will result in a voided warranty.
- When installing this product take into account the surface temperature of the material this product is mounted to. Many building surfaces which are exposed to direct sunlight exceed the 70° C / 158° F maximum that our product is rated for. High risk locations like this should be avoided.
- Our IP65 can be used in wet, outdoor locations around swimming pools and spa tubs, but our products are not intended to be submerged in pools and fountains and do not carry UL676 certification to do so.
- Please refer to our RibbonLyte Proper Use Guide in our Application Guide for more information. Available for download at www.GENLEDBrands.com/Acolyte.
- Compatible with a wide variety of control products including the entire line of Lutron dimming systems.
- For use with Acolyte drivers, 0-10V dimming modules and interface controllers (DMXINF models).
- Use with non-Acolyte supplied drivers is not supported or warrantied.
- Due to the nature of the product, RibbonLyte cuttable lengths are generally longer or shorter than the customer requested length. Unless specified, RibbonLyte is factory cut at the shorter cuttable point.
- We reserve the right to make changes to product lineup, specifications, design and finishes at any time without notice.

Acolyte does not warrant or represent that the information is free from errors or omission. The information may change without notice and Acolyte is not in any way liable for the accuracy of any information printed and stored or in any way interpreted or used.




CHANNEL COMPATIBILITY / CHANNEL OPTIONS

	IP20 IP65	IP68	SURFACE MOUN	TED CHANNELS						
AC1	/	~	LENS OPTIONS:	C - Clear F - Fr	osted K - Black	M - Milky NP - Na	rrow Prismatic W	P - Wide Prismatic	RM - Round Milky	SM - Square Milky
AC2	/	/								
AC3	/	/								
AC4	✓	✓								
AC5	/	/								
AC14	✓							6. 40		
AP1	/	/	AC1	AC2	AC3	AC4	AC5	AC14	AP1	AS1
AR1	✓		C, F, M	C, F, M	C, F, M	C, F, M	C, F, M	SM	C, K, M, SM	C, F, M
AR2	/	/							b	
AR3	/	/								
AR5	/									
AR8	/								i i	
AR10	/		AS2	AS3	AS6	AS10	AS12	AS13	AS14	AS16
AR14	/		C, F, M	C, F, M	C, F, M	C, M	RM	RM, SM	SM	C, K, M
AR16	/	/	_							
AR20	/	1								
AR23	/	•								
AR25	/	/						0	0 0	9
AR30	/	/	AS20G	AS23	AS28	AS30	AS53	AT4	AT5	AT11
AR33	/	/	G	C, K, M, SM	M, NP, WP	M, RM, SM	M, NP, WP	C, F, M	C, F, M	C, F, M
AR33 AS1	/	~	_	_					_	
		✓							17	
AS2	/		A						· //	
AS3	/	✓ ✓				1		l.		
AS6	/	~	A14/10	AW12	AW14	A14/7E	AW38	A)4/70	D1	D2
AS10	/		AW10 C, K, M	C, K, M, RM	C, K, M	AW35 C, F, M	M, RM, SM	AW38 C, F, M	B1 C, F, M	B2 RM
AS12	/	~								
AS13	/	~								
AS14	/									
AS16	/	~			0 0	60				
AS20G	/								@ (*)	
AS23	/	/	C22	GL2	ROUND	ROUND12	ROUND20	ST10	WH35	
			CEM	CEM	CEM	CKM	CKM	CEM	CEM	
	~	/	C, F, M	C, F, M	C, F, M	C, K, M	C, K, M	C, F, M	C, F, M	
AS30	✓ ✓	~	C, F, M	C, F, M	C, F, M	C, K, M	C, K, M	C, F, M	C, F, M	
AS30 AS53	✓ ✓	✓ ✓			C, F, M	С, К, М	С, К, М	C, F, M	C, F, M	
AS30 AS53 AT4	~	~	C, F, M		C, F, M	C, K, M	C, K, M	C, F, M	C, F, M	
AS30 AS53 AT4 AT5	✓ ✓	✓ ✓	RECESSED CHAN	NNELS	C, F, M		C, K, M		C, F, M RM - Round Milky	SM - Square Milky
AS28 AS30 AS53 AT4 AT5 AT11	\rangle \rangl	\rightarrow \right	RECESSED CHAN	NNELS						SM - Square Milky
AS30 AS53 AT4 AT5	\rightarrow	\rightarrow \right	RECESSED CHAN	NNELS						SM - Square Milky
AS30 AS53 AT4 AT5 AT11	\rangle \rangl	\rightarrow \right	RECESSED CHAN	NNELS						SM - Square Milky
AS30 AS53 AT4 AT5 AT11 AW10 AW12		\rightarrow \right	RECESSED CHAN	NNELS						SM - Square Milky
AS30 AS53 AT4 AT5 AT11 AW10		\rightarrow \right	RECESSED CHAN	NNELS						SM - Square Milky
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35		\rightarrow \right	RECESSED CHAN	NNELS C - Clear F - Fr	osted K - Black	M - Milky NP - Na	rrow Prismatic W	P - Wide Prismatic	RM - Round Milky	
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14		\rightarrow \right	RECESSED CHAN	NNELS						SM - Square Milky AR16 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	\rightarrow \right	RECESSED CHAP LENS OPTIONS:	NNELS C - Clear F - From AR2	osted K - Black	M - Milky NP - Na	rrow Prismatic W	P - Wide Prismatic	RM - Round Milky AR14	AR16
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38		\rightarrow \right	RECESSED CHAP LENS OPTIONS:	NNELS C - Clear F - From AR2	osted K - Black	M - Milky NP - Na	rrow Prismatic W	P - Wide Prismatic	RM - Round Milky AR14	AR16
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1		\rightarrow \right	RECESSED CHAP LENS OPTIONS:	NNELS C - Clear F - From AR2	osted K - Black	M - Milky NP - Na	rrow Prismatic W	P - Wide Prismatic	RM - Round Milky AR14	AR16
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2		\rightarrow \right	RECESSED CHAP LENS OPTIONS:	NNELS C - Clear F - From AR2	osted K - Black	M - Milky NP - Na	rrow Prismatic W	P - Wide Prismatic	RM - Round Milky AR14	AR16
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	\rightarrow \right	RECESSED CHAN LENS OPTIONS:	NNELS C - Clear F - From AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5	AR8 C, F, M	P - Wide Prismatic AR10 C, M	RM - Round Milky AR14 SM	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2		\rightarrow \right	RECESSED CHAR LENS OPTIONS:	AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5 M	AR8 C, F, M	P - Wide Prismatic AR10 C, M	RM - Round Milky AR14 SM SC1	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND		\rightarrow \right	RECESSED CHAN LENS OPTIONS:	NNELS C - Clear F - From AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5	AR8 C, F, M	P - Wide Prismatic AR10 C, M	RM - Round Milky AR14 SM	AR16 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND		\rightarrow \right	RECESSED CHAR LENS OPTIONS:	AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5 M	AR8 C, F, M	P - Wide Prismatic AR10 C, M	RM - Round Milky AR14 SM SC1	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND		\rightarrow \right	RECESSED CHAR LENS OPTIONS:	AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5 M	AR8 C, F, M	P - Wide Prismatic AR10 C, M	RM - Round Milky AR14 SM SC1	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND20 SC1		\rightarrow \right	RECESSED CHAR LENS OPTIONS:	AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5 M	AR8 C, F, M	P - Wide Prismatic AR10 C, M	RM - Round Milky AR14 SM SC1	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND20 SC1		\rightarrow \right	RECESSED CHAR LENS OPTIONS:	AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5 M	AR8 C, F, M	P - Wide Prismatic AR10 C, M	RM - Round Milky AR14 SM SC1	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND12 ROUND20 SC1 SC2 SC3		\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	AR1 C, F, M AR20 C, K, M, SM	AR2 C, F, M	AR3 C, F, M AR25 M, RM, SM	M - Milky NP - Na AR5 M AR30 M, RM, SM	AR8 C, F, M AR33 M, NP, WP	AR10 C, M GL1 C, F, M SC-CORNER2	RM - Round Milky AR14 SM SC1 M	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND20 SC1 SC2 SC3 SC4		\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	ARI C, F, M	AR2 C, F, M	AR3 C, F, M	M - Milky NP - Na AR5 M AR30 M, RM, SM	AR8 C, F, M AR33 M, NP, WP	ARIO C, M	RM - Round Milky AR14 SM SC1 M	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND12 ROUND20 SC1 SC2 SC3 SC4			AR1 C, F, M AR20 C, K, M, SM	AR2 C, F, M	AR3 C, F, M AR25 M, RM, SM	M - Milky NP - Na AR5 M AR30 M, RM, SM	AR8 C, F, M AR33 M, NP, WP	AR10 C, M GL1 C, F, M SC-CORNER2	RM - Round Milky AR14 SM SC1 M	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND12 ROUND20 SC1 SC2 SC3 SC4 SC5 SC6		\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	AR1 C, F, M AR20 C, K, M, SM	AR2 C, F, M	AR3 C, F, M AR25 M, RM, SM	M - Milky NP - Na AR5 M AR30 M, RM, SM	AR8 C, F, M AR33 M, NP, WP	AR10 C, M GL1 C, F, M SC-CORNER2	RM - Round Milky AR14 SM SC1 M	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND12 ROUND20 SC1 SC2 SC3 SC4 SC5 SC6 SC-CORNER1			ARI C, F, M AR20 C, K, M, SM SC3 M	AR2 C, F, M	AR3 C, F, M AR25 M, RM, SM	M - Milky NP - Na AR5 M AR30 M, RM, SM	AR8 C, F, M AR33 M, NP, WP	AR10 C, M GL1 C, F, M SC-CORNER2	RM - Round Milky AR14 SM SC1 M	ARI6 C, K, M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND12 ROUND20 SC1 SC2 SC3 SC4 SC5 SC6 SC-CORNER1 SC-CORNER1			RECESSED CHAN LENS OPTIONS: AR1 C, F, M AR20 C, K, M, SM SC3 M DISCLAIMER	AR2 C, F, M AR2 C, F, M SC4 M, RM, SM	AR3 C, F, M AR25 M, RM, SM	M - Milky NP - Na AR5 M AR30 M, RM, SM SC6 C, K, M, SM	AR8 C, F, M AR33 M, NP, WP	AR10 C, M	RM - Round Milky AR14 SM SC1 M W31 C, F, M	ARI6 C, K, M SC2 M
AS30 AS53 AT4 AT5 AT11 AW10 AW12 AW14 AW35 AW38 AW40 B1 B2 C22 GL1 GL2 ROUND ROUND12 ROUND12 ROUND20 SC1 SC2 SC3 SC4 SC5 SC6 SC-CORNER1			ARI C, F, M AR20 C, K, M, SM DISCLAIMER When installing to	AR2 C, F, M AR23 C, K, M SC4 M, RM, SM	AR3 C, F, M AR25 M, RM, SM	M - Milky NP - Na AR30 M, RM, SM SC6 C, K, M, SM	AR8 C, F, M AR33 M, NP, WP SC-CORNERI M	ARIO C, M GL1 C, F, M SC-CORNER2 M	AR14 SM SC1 M W31 C, F, M	AR16 C, K, M SC2 M



WIRING DIAGRAMS



WIRE COLORS PER RIBBONLYTE COLOR

STATIC WHITE SERIES 2 Red Wire (+) Positive Black Wire (-) Negative